



FOCAL LENGTH (EFL): 60 ±0,6  
 BACK FOCAL LENGTH (BFL): 58,08

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	54,136±0,054 CX	GLASS FUSED SILICA 458/678	R	54,136±0,054 CX
Øe	24		Øe	24
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION		
ROHS: COMPLIANT	SCALE: NONE λ = 587,6nm			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE 25mm Dia, x 60mm FL, Uncoated, UV Double-Convex Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN: mm	DWG NO 48295
INDICATIONS IN ACCORDANCE WITH ISO 10110				SHEET 1 OF 1