




NOTES:

1. SUBSTRATE: FUSED SILICA
2. COATING (APPLY ACROSS COATING APERTURE):
S1 & S2: NONE
3. EFFECTIVE FOCAL LENGTH: 18.80mm
4. DIVERGENCE ANGLE: $\pm 0.5^\circ$
5. WAVELENGTH RANGE (nm): 200 - 2200
6. ROHS: COMPLIANT




DETAIL A



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	MICROLENS ARRAY 10 x 10mm, 300µm PITCH, 0.5° DIVERGENCE	
ALL DIMS IN	mm	DWG NO	64478	SHEET 1 OF 1