

TECHSPEC® HPr SERIES

FIXED FOCAL LENGTH LENSES

#35-152 • 8.5mm • f/8.0

Designed with a high level of machine vision performance in mind, TECHSPEC® HPr Series Fixed Focal Length Lenses are stability ruggedized with all individual lens elements glued in place to reduce object shift on the image. Additionally, they feature robust mechanical components with a simplified focus and stainless steel locking C-Mount clamp. These lenses are exemplary for calibrated imaging systems.



| | |
|--------------------------------------|----------|
| Focal Length: | 8.5mm |
| Working Distance¹: | 75mm - ∞ |
| Max. Sensor Format: | 2/3" |
| Camera Mount: | C-Mount |
| Aperture (f/#): | f/8.0 |
| Distortion %²: | <7.77% |
| Object Space NA²: | 0.005596 |

1. From front housing 2. At Minimum W.D.

| | |
|-------------------------------------|---------------------------|
| Magnification Range: | 0X - 0.092X |
| Type: | Fixed Focal Length Lens |
| Length: | 44.57mm |
| Weight: | 106g |
| RoHS: | Compliant |
| Stability Ruggedized: | <1 µm pixel shift at 50 G |
| Number of Elements (Groups): | 9 (8) |
| AR Coating: | 425 - 675nm BBAR |

| At Minimum W.D. (75mm) | | | | | | |
|----------------------------|----------------|----------------|----------------|----------------|----------------|-----------------|
| Sensor Size | 1/4" | 1/3" | 1/2.5" | 1/2" | 1/1.8" | 2/3" |
| Field Of View ³ | 39.6mm - 24.1° | 53.2mm - 32.0° | 64.8mm - 38.4° | 71.9mm - 42.2° | 81.5mm - 47.2° | 101.4mm - 56.8° |

3. Horizontal FOV on Standard (4:3) sensor format. Min W.D.




Figure 1: Distortion at the maximum sensor format. Positive values correspond to pincushion distortion, negative values correspond to barrel distortion.




Figure 2: Relative illumination (center to corner)

In both plots, field points corresponding to the image circle of common sensor formats are included. Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

MTF & DOF: f/8.0
WD: 167mm
HORIZONTAL FOV: 200mm




Figure 3: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are the Tangential and Sagittal values for field points on center, at 70% of full field and the maximum sensor format. Solid black line indicates diffraction limit determined by f/#-defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 4: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

MTF & DOF: f/8.0
WD: 444mm
HORIZONTAL FOV: 500mm




Figure 5: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are the Tangential and Sagittal values for field points on center, at 70% of full field and the maximum sensor format. Solid black line indicates diffraction limit determined by f/#-defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 6: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.