NOTES:


MATERIAL:


HOUSING: STAINLESS STEEL LENS: D-ZLaF52LA


2. COATING (APPLY ACROSS CLEAR APERTURE) R(AVG) <0.4% @ 600 - 1050nm

3. CLEAR APERTURE: 5.00 mm

4. RoHS: COMPLIANT







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

	dmund	Optics®
--	-------	---------

THIRD ANGLE PROJECTION	\$	TITLE	780nm Alignment, 0.40 NA Fiber Collimator FC Connector	
ALL DIMS IN	mm	DWG NO	64771	SHEET 1 OF 1