## NOTES:


1. MATERIAL:


HOUSING: STAINLESS STEEL LENS: D-ZLaF52LA

2. COATING (APPLY ACROSS CLEAR APERTURE) R(AVG) <0.4% @ 1050 - 1600nm

3. CLEAR APERTURE: 5.00 mm

4. RoHS: COMPLIANT





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

## **Edmund Optics**®

THIRD ANGLE PROJECTION TITLE 1064nm Alignment, 0.40 NA Fiber Collimator w/ SMA Connector

ALL DIMS IN mm DWG NO 64774 SHEET 1 OF 1

## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING