## NOTES:

1. MATERIAL:


HOUSING: STAINLESS STEEL LENS: D-ZLaF52LA


2. COATING (APPLY ACROSS CLEAR APERTURE) R(AVG) <0.4% @ 1050 - 1600nm

3. CLEAR APERTURE: 4.95 mm

4. RoHS: COMPLIANT







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

## **Edmund Optics**®

THIRD ANGLE TITLE 1310nm Alignment, 0.55 NA Fiber Collimator w/ FC Connector

ALL DIMS IN mm DWG NO 64791 SHEET 1 OF 1

