




NOTES:

- 1. RoHS: EXEMPT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
NUMBER OF LENSES	6
FIELD OF VIEW, 2/3" SENSOR (mm)	11.00
OBJECT TO IMAGE TRACK LENGTH (mm)	106.90
OBJECT DISTANCE (mm)	38.40
APERTURE	f/8
IMAGE DISTANCE (mm)	38.40
MAX SENSOR FORMAT	2/3"



ALL DIMS IN mm



TITLE	30mm F8 RELAY ASSEMBLY		
DWG NO	45762	SHEET	1 OF 1