


Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


400nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


400nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


450nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


450nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


500nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


500nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


550nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


550nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


600nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


600nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


650nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


650nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

700nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

700nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY

