




- NOTES:
- 1. CONSTRUCTION: BLACK ANODIZED ALUMINUM
 - 2. TECHNOLOGY: Hexa-Black™
 - 3. ABSORBANCE (%): 99.9
 - 4. WAVELENGTH RANGE (nm): 200 - 5,000

HEXA-BLACK STRUCTURE
FOR REFERENCE



INSIDE OF EXTENSION TUBE
IS COVERED IN HEXA-BLACK



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

Edmund Optics®

THIRD ANGLE PROJECTION		TITLE		5mm Length, Acktar Hexa-Black™ C-Mount Noise Reduction Extension Tube	
ALL DIMS IN	mm	DWG NO	15479	SHEET 1 OF 1	