



NOTES:

- 1. SUBSTRATE MATERIAL: N-BK7
- 2. ROHS COMPLIANT
- 3. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: R(AVG) > 98% @ 340 - 488nm @ 0°, ALL POLARIZATIONS
 - R(AVG) > 98% @ 320 - 450nm @ 45°, ALL POLARIZATIONS
 - R(AVG) > 99% @ 320 - 450nm @ 45°, S-POLARIZATION


S2: NONE

4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	PLANO	PLANO				
ANGLE TOL. (arcmin)	±2	±2				
SURFACE QUALITY	40-20	40-20				
SURFACE FLATNESS	λ/8	λ/8				
CLEAR APERTURE	90%	90%				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				
			THIRD ANGLE PROJECTION		TITLE	5.0mm 320 - 450nm COATED, N-BK7 RIGHT ANGLE MIRROR
			ALL DIMS IN	mm	DWG NO	15593
						SHEET 1 OF 1

 Edmund Optics®