





NOTES:

1. SUBSTRATE: COLORED GLASS



LONGPASS FILTER

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
$\Delta\lambda$	<60
TH (%)	N/A
CUT-ON WAVELENGTH (nm)	830±10
SURFACE QUALITY	60-40
WAVELENGTH	IR
BEVEL	PROTECTIVE AS NEEDED

 **Edmund Optics®**



ALL DIMS IN

mm

TITLE

Hoya IR83N (830nm), 25.4mm Dia., 2.5mm
Thick, Colored Glass Longpass Filter

DWG NO

18898

SHEET
1 OF 1