


NOTES:

1. COATING (APPLY ACROSS COATING APERTURE)

DURABILITY: MIL-C-48497A
PERFORMANCE SPECIFICATIONS:
CWL: 457
FWHM: 8 NOMINAL
TRANSMISSION %: 77% (400-435); 87% (500-1500nm)

2. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS
APPLY ACROSS CLEAR APERTURE

3. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® Edmund Optics®

	S1	S2				NOTCH FILTER	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	23030	SHEET 1 OF 3