





- NOTES:
- 1. COATING:  
S1: METAL VELVET™  
THICKNESS: 5-7(μm)
  - 2. ABSORBANCE: 99.9 (0 - 10° AOI) %
  - 3. ABRASION RESISTANCE: LIGHT, DO NOT TOUCH
  - 4. HUMIDITY RESISTANCE: MIL-C-48497A
  - 5. OPERATING TEMPERATURE (°C): -196 TO +350
  - 6. WAVELENGTH RANGE (μm): 0.3 - 14



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	10 x 10cm Sheet of Metal Velvet Foil, No Adhesive
ALL DIMS IN	mm	DWG NO	28937
			SHEET 1 OF 1