






- NOTES:
- 1. COATING:
S1: MAXIBLACK™
THICKNESS: 4 - 6 (µm)
 - 2. ABSORBANCE: 98%
 - 3. ABRASION RESISTANCE: MODERATE
 - 4. HUMIDITY RESISTANCE: MIL-C-48497A
 - 5. OPERATING TEMPERATURE (°C): -250 TO +290
 - 6. WAVELENGTH RANGE (µm): 0.3 - 5



DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	10 x 10cm Sheet of MaxiBlack Film, No Adhesive
ALL DIMS IN	mm	DWG NO	28943
			SHEET 1 OF 1