




NOTES:

- 1. SUBSTRATE: Polymer Film XP40HT-18
- 2. WAVELENGTH RANGE: 400 - 700 nm
- 3. POLARIZATION EFFICIENCY (%): >99.5
- 4. TRANSMISSION (%):
 - SINGLE: 40 ±2
 - PARALLEL: 32.2
 - CROSSED: <0.005
- 5. EXTINCTION RATIO: 5000:1
- 6. TEMPERATURE RESISTANCE (°C x HOURS):
 - HEAT: 100 x 1,000
 - COLD: -40 x 1,000
 - HUMIDITY: 80 x 90% RH x 1,000
- 7. ROHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

THIRD ANGLE PROJECTION 		 Edmund Optics®		
TITLE		600 x 1000mm High-Temperature Linear Polarizing Film (XP40HT-18)		
ALL DIMS IN	mm	DWG NO	29464	SHEET 24 OF 50