




NOTES:


- 1. CUT-ON WAVELENGTH: 675±13.5nm
- 2. BLOCKING RANGE: 698.8 - 777.3nm
- 3. TRANSMISSION RANGE: >85% @ 400 - 651.6nm
- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	675nm 12.45mm, Ultra-Thin OD 4.0 Shortpass Filter	
ALL DIMS IN	mm	DWG NO	29205	SHEET 19 OF 24