

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

TECHSPEC® C Series Fixed Focal Length SWIR Lenses



- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Compact (C) SWIR Lens for 900-1700nm Wavelength Range
- 3.5mm to 100mm Focal Length

Common Specifications

General

Imaging Lens Type: Compact Lens

Physical & Mechanical Properties

Iris Option: Variable

Optical Properties

Wavelength Range (nm): 900 - 1700

Coating: 900 - 1700nm BBAR

Coating Specification: 900 - 1700nm BBAR

Threading & Mounting

Mount: C-Mount

Environmental & Durability Factors

Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Technical Information

Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Mount	Stock Number	Price	Buy
#23-216 New							
							
New							
Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!							
3.50	1/1.8"	f/2 - f/11	0 - ∞	C-Mount		€620,00	3-4 days
#23-217 New							
							
New							
Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!							
4.50	1/1.8"	f/2 - f/11	25 - ∞	C-Mount		€620,00	Contact Us
6.00	1/1.8"	f/1.4 - f/16	75 - ∞	C-Mount	#23-218	€503,00	3-4 days

8.50	2/3"	f/1.3 - f/16	100 - ∞	C- Mount	#23-219	€503,00	3-4 days
12.00	2/3"	f/1.8 - f/16	100 - ∞	C- Mount	#23-220	€503,00	3-4 days
16.00	2/3"	f/1.6 - f/16	100 - ∞	C- Mount	#23-221	€438,00	3-4 days
25.00	2/3"	f/1.4 - f/16	100 - ∞	C- Mount	#23-222	€438,00	3-4 days
35.00	2/3"	f/1.65 - f/22	165 - ∞	C- Mount	#23-223	€438,00	3-4 days
50.00	2/3"	f/2 - f/22	250 - ∞	C- Mount	#23-224	€483,00	3-4 days

[#23-225 New](#)



New

Launched
on our
website
before
appearing
in our
latest print
catalogs.
Be the
first to buy
before
anyone
else!

100.00 4/3" f/2.8 - f/22 750 -
∞ C-
Mount

€595,00

Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com