

[See all 14 Products in Family](#)

# LightPath 354061 | 6.33mm Dia., 0.24 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock #83-701 **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €75.<sup>00</sup>

**ADD TO CART**

#### Volume Pricing

Qty 1-10	€75,00 each
Qty 11-49	€67,50 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

#### Product Downloads

#### General

354061 **Lightpath Lens Code:**

Aspheric Lens **Type:**

#### Physical & Mechanical Properties

**Diameter (mm):**

6.33 ±0.015

Clear Aperture CA (mm):

5.20

Edge Thickness ET (mm):

1.64

Center Thickness CT (mm):

2.43 ±0.05

Bevel:

Protective as needed

## Optical Properties

Effective Focal Length EFL (mm):

11.00 @633nm

Numerical Aperture NA:

0.24

Substrate:

[D-ZK3](#)

Focal Length Tolerance (%):

±1

Aspheric Design Wavelength (nm):

633

Coating:

BBAR (350-700nm)

Coating Specification:

$R_{avg} \leq 0.5\%$  @ 350 - 700nm

Surface Quality:

60-40

f#:

2.08

Abbe Number ( $v_d$ ):

61.16

Index of Refraction ( $n_d$ ):

1.589

Wavelength Range (nm):

350 - 700

Working Distance (mm):

9.600

Conjugate Distance:

Infinite

Focal Length Specification Wavelength (nm):

633.00

Transmitted Wavefront Error ( $\lambda$ , RMS):

< 0.178

## Material Properties

Coefficient of Thermal Expansion CTE ( $10^{-6}/^{\circ}\text{C}$ ):

7.6

## Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Compliant](#)

## Product Details

- Compact, Molded Aspheric Lens Design
- Improved Performance Compared to Doublet and Triplet Lenses
- Ideal for Laser Tools and Measurement Systems

LightPath® Laser Tool Molded Aspheric Lenses are designed to fulfill the needs of a variety of tools and measurement systems utilizing laser diodes, including leveling lasers, projectors, scanners, trackers, and gun sights. By utilizing a single aspheric lens, the need for a multi-lens system is eliminated, allowing for a more compact and robust design. Each aspheric lens is offered with various anti-reflection coatings for optimum transmission in the visible and NIR wavelength ranges. LightPath® Laser Tool Molded Aspheric Lenses' anti-reflection coating options for each lens provides <1% average reflection over the entire design wavelength range. The lenses are offered in four different diameters: 3mm, 4.70mm, 6mm, and 6.33mm.

**LASER OPTICS** MADE BY EDMUND OPTICS®

[LEARN MORE](#)

