

0.33X Mag, InfiniGage Precision Spacer

See More by [Infinity Photo-Optical Company](#)



Stock #62-846 **1 In Stock**

⊖ 1 ⊕ €78.⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | €78,00 each |
| Need More? | Request Quote |

⚠ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Lens Accessory Type:
Compatible Lens:
[#62-830](#) & [#62-831](#)

Optical Properties

Horizontal Field of View, 1/2" Sensor:
 19.4mm
 Horizontal Field of View, 1/3" Sensor:

14.6mm

120.00 **Working Distance (mm):**

0.33X **Magnification:**

Threading & Mounting

C-Mount **Mount:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

Product Details

- Accurate Measurements Based on Field of View
- 7 Spacer Options for a Wide Range of Magnifications
- UV Option Available

The InfiniGage™ main lens mates with seven precision spacers for multiple magnification and working distance choices. Simply set InfiniGage™ to the desired magnification and begin making accurate measurements. The InfiniGage™ accepts 11.8mm to 12.5mm diameter filters for polarization or color analysis without changing outer dimensions. The InfiniGage™ can be doubled in magnification by simply adding a DL Doubler Tube, reducing the FOV by a factor of two. The InfiniGage™ is also available in UV which is optimized for best performance from 250nm-700nm.

Note: InfiniGage™ CW option is only compatible with CW Precision Spacers.

Technical Information

| | Magnification | Working Distance | Field of View on 1/2" Sensor | Field of View on 1/3" Sensor |
|--|---------------|------------------|------------------------------|------------------------------|
| InfiniGage Precision Spacer with 2X Amplifier (Optional) | 0.25X | 286mm | 25.6mm | 19.2mm |
| | 0.5X | 155mm | 12.8mm | 9.6mm |
| | 0.66X | 120mm | 9.7mm | 7.3mm |
| | 1.0X | 85mm | 6.4mm | 4.8mm |
| | 1.3X | 72mm | 4.9mm | 3.6mm |
| | 1.5X | 67mm | 4.3mm | 3.2mm |
| | 2.0X | 52mm | 3.2mm | 2.4mm |