

[See all 75 Products in Family](#)

LightPath 354125 | 11mm Dia., 0.50 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#33-425** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €119.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€119,00 each
Qty 11-49	€107,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Thickness: 0.25 (t) (mm)
Material: B-K7

Compatible Window:

354125

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:
Collimate or Focus Laser Light

Physical & Mechanical Properties

Diameter (mm):

11.00 ±0.015

Clear Aperture CA (mm):

10

Edge Thickness ET (mm):

1.092

Center Thickness CT (mm):

3.64 ±0.40

Bevel:

Protective as needed

Optical Properties

Effective Focal Length EFL (mm):

10.00 @ 633nm

Numerical Aperture NA:

0.50

Substrate:

[D-ZK3](#)

Focal Length Tolerance (%):

±1

Aspheric Design Wavelength (nm):

633

Coating:

BBAR (350-700nm)

Coating Specification:

$R_{avg} \leq 0.5\%$ @ 350 - 700nm

Surface Quality:

60-40

f##:

1.00

Abbe Number (v_d):

60.88

Index of Refraction (n_d):

1.586

Wavelength Range (nm):

350 - 700

Working Distance (mm):

7.8

Conjugate Distance:

Infinite

Focal Length Specification Wavelength (nm):

633.00

Transmitted Wavefront Error (λ , RMS):

< 0.09

Material Properties

Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$):

7.6

Environmental & Durability Factors

Operating Temperature ($^{\circ}\text{C}$):

≤200

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Compliant](#)

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.

Technical Information

