

[See all 75 Products in Family](#)

# LightPath 355151 | 3mm Dia., 0.50 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#83-582** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €75.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€75,00 each
Qty 11-49	€67,50 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

Thickness: 0.25 (t) (mm)  
Material: BK7

Compatible Window:

355151

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:  
Collimate or Focus Laser Light

## Physical & Mechanical Properties

Diameter (mm):  
3.00 ±0.015

Clear Aperture CA (mm):  
2

Edge Thickness ET (mm):  
1.40

Center Thickness CT (mm):  
1.89 ±0.03

Bevel:  
Protective as needed

Distance from Window to Lens (D) (mm):  
0.479

## Optical Properties

Effective Focal Length EFL (mm):  
2.00 @ 780nm

Numerical Aperture NA:  
0.50

Substrate:   
[D-ZLaF52LA](#)

Focal Length Tolerance (%):  
±1

Aspheric Design Wavelength (nm):  
780

Coating:  
BBAR (350-700nm)

Coating Specification:  
 $R_{avg} \leq 0.5\%$  @ 350 - 700nm

Surface Quality:  
40-20

f#:  
1.00

Abbe Number ( $v_d$ ):  
40.79

Index of Refraction ( $n_d$ ):  
1.806

Wavelength Range (nm):  
350 - 700

Working Distance (mm):  
1.029

Conjugate Distance:  
Infinite

Focal Length Specification Wavelength (nm):  
780.00

Transmitted Wavefront Error ( $\lambda$ , RMS):  
< 0.07

## Material Properties

Coefficient of Thermal Expansion CTE ( $10^{-6}/^{\circ}\text{C}$ ):  
6.9

## Environmental & Durability Factors

Operating Temperature ( $^{\circ}\text{C}$ ):  
≤200

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 247:  
[Compliant](#)

## Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam

shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.

# LASER OPTICS MADE BY EDMUND OPTICS®



LEARN MORE

## Technical Information

