

[See all 75 Products in Family](#)

LightPath 354453 | 6mm Dia., 0.55 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-159** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €75.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€75,00 each
Qty 11-49	€67,50 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Thickness: 0.28 (t) (mm)
Material: BK7

Compatible Window:

354453

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:
Collimate or Focus Laser Light

Physical & Mechanical Properties

Diameter (mm):
6.00 ±0.020

Clear Aperture CA (mm):
4.8

Edge Thickness ET (mm):
1.75

Center Thickness CT (mm):
3.14 ±0.02

Bevel:
Protective as needed

Distance from Window to Lens (D) (mm):
2.049

Optical Properties

Effective Focal Length EFL (mm):
4.60 @ 655nm

Numerical Aperture NA:
0.55

Substrate:
[D-ZK3](#)

Focal Length Tolerance (%):
±1

Aspheric Design Wavelength (nm):
655

Coating:
BBAR (1050-1600nm)

Coating Specification:
R_{abs} <1.0% @ 1050 - 1600nm

Surface Quality:
40-20

f#:
0.91

Abbe Number (v_d):
60.88

Index of Refraction (n_d):
1.586

Wavelength Range (nm):
1050 - 1600

Working Distance (mm):
2.7

Conjugate Distance:
Infinite

Focal Length Specification Wavelength (nm):
655.00

Transmitted Wavefront Error (λ, RMS):
< 0.09

Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
7.6

Environmental & Durability Factors

Operating Temperature (°C):
≤200

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures


LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam

shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)

Technical Information



Compatible Mounts