

TECHSPEC[®] 0.5X, 110mm WD, In-Line CompactTL[™] Telecentric Lens



110mm WD, 0.5X, In-Line Version (Left) and VS Version (Right)



Stock **#67-303** 16 In Stock

-

1

+

€1.065⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.065,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
CompactTL [™] Series	Series:
Edmund Optics [®]	Manufacturer:
Telecentric Lens	Type:


Compatible Light Guide/Source: 1/4" (0.312") and 1/8" (0.187")	
In-Line Illumination	Type of Illumination:
Physical & Mechanical Properties	
Fixed	Iris Option:
170.00	Length (mm):
170.00	Length excluding Threads (mm):
40.00	Maximum Diameter (mm):
193	Weight (g):
Optical Properties	
17.6mm	Horizontal Field of View, 2/3" Sensor:
12.8mm	Horizontal Field of View, 1/2" Sensor:
9.6mm	Horizontal Field of View, 1/3" Sensor:
11.00	Maximum Image Circle (mm):
0.027	Numerical Aperture NA, Object Side:
±1	Working Distance Tolerance (mm):
5 (5)	Number of Elements (Groups):
0.064	Typical Telecentricity @ 588nm (°):
0.0202	Typical Distortion @ 588nm (%):
0.5X	Primary Magnification PMAG:
0.50	Telecentric Lens Magnification:
110	Working Distance (mm):
17.6 x 13.2	FOV @ Max Sensor Format, H x V (mm):
f/9.3	Aperture (f/#):
λ/4 MgF ₂	Coating:
±1.9mm (20% @ 20 lp/mm)	Depth of Field (mm):
0.5X	Magnification:
VIS	Lens Wavelength Range:
Sensor	
2/3"	Maximum Sensor Format:
4.50	Pixel Size (µm):
Threading & Mounting	
M37 x0.75 (Female)	Filter Thread:
C-Mount	Mount:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details


- 2/3", C-Mount Telecentric Lens
- Up to 2.3 MegaPixels, 4.5µm Pixel Size Sensors
- Small Telecentric Lens with Coaxial Illumination Options

TECHSPEC® CompactTL™ Telecentric Lenses are designed for applications with tight space constraints due to their ultra-compact design. These lenses feature a 2/3" sensor format and a variety of different working distance and magnification options. From single unit to high volume implementation, these lenses provide a great price to performance ratio. TECHSPEC® CompactTL™ Telecentric Lenses are perfect for integration into gauging systems due to their excellent telecentricity and low distortion. The fixed iris and lockable focus make these lenses ideal for implementation into factory floors and assembly lines, as they will remain fixed over time.


Technical Information




#67-303, 0.5X, 110mm WD, In-Line CompactTL™ Telecentric Lens, Distortion Plot



#67-303, 0.5X, 110mm WD, In-Line CompactTL™ Telecentric Lens, Relative Illumination Plot



#67-303, 0.5X, 110mm WD, In-Line CompactTL™ Telecentric Lens, Telecentricity Plot



#67-303, 0.5X, 110mm WD, In-Line CompactTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 110mm Working Distance, f9.3



#67-303, 0.5X, 110mm WD, In-Line CompactTL™ Telecentric Lens, Depth of Field Plot, 110mm Working Distance, f9.3