

0.69X 65mm WD, In-Line Illumination 1.2" Telecentric Lens



1.2" Sensor In-Line Illumination Telecentric Lenses

Stock **#72-171** **2 In Stock**

⊖ 1 ⊕ €4.050⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€4.050,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Series:
1.2" Sensor In-Line Illumination Telecentric Lenses

Type:
Telecentric Lens

Compatible Light Guide/Source:
1/4" (0.312")

Type of Illumination:
In-Line Illumination

Physical & Mechanical Properties

160.00 Length (mm):

0.312 Ferrule Diameter (inches):

19.3 Maximum Diameter (mm):

Optical Properties

21.01mm Horizontal Field of View @ Max Sensor Format:

11.6mm Horizontal Field of View, 2/3" Sensor:

9.8mm Horizontal Field of View, 1/2" Sensor:

19.30 Maximum Image Circle (mm):

0.69X Primary Magnification PMAG:

0.69 Telecentric Lens Magnification:

65.00 Working Distance (mm):

f/6.0 Aperture (f#):

<0.01% Distortion (%):

0.69X Magnification:

VS Lens Wavelength Range:

Sensor

1.2" Maximum Sensor Format:

2.74 Pixel Size (µm):

Threading & Mounting

N/A Filter Thread:

C-Mount Mount:

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- 1.2" Max Sensor Format
- Fiber Optic Input for In-line Illumination
- Long Working Distance

1.2" Sensor In-Line Illumination Telecentric Lenses are designed for cameras with SONY IMX367, 530, and 540 or equivalents allowing for large fields of view. These lenses are designed with an in-line illumination port that accepts a 1/4" fiber optic light guide with incorporated M3 set screws in the in-line illumination port to light guide and include a lockable ring to rotate the lens and ensure alignment with the camera sensor. These telecentric lenses are designed to achieve high coaxial uniformity on 3µm, 24.5MP sensors and reduce parallax errors yielding maximum image quality with an excellent degree of measurement accuracy. 1.2" Sensor In-Line Illumination Telecentric Lenses are available in magnifications ranging from 0.5X–3.45X and offer low f/#s and a low distortion of <0.01%. These lenses are ideal for applications including machine vision, metrology, automotive and electronic inspection, measurement, and gauging.

Note: 1/4" [Fiber optic light guides](#) are sold separately.