

## 1.0 OD 75 x 75mm Neutral Density Filter



Stock #53-705 **20+ In Stock**

⊖ 1 ⊕ €252.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€252,00 each
Qty 11-49	€211,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Neutral Density Filter **Type:**

### Physical & Mechanical Properties

75 x 75 (Nominal) **Dimensions (mm):**

75.00 **Length (mm):**

Width (mm):  
75.00

## Optical Properties

Optical Density OD (Average):  
1.0

Substrate:   
Wratten 2

Coating:  
Uncoated

Transmission (%):  
10.00

Blocking Wavelength Range (nm):  
400 - 700

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Reach 223:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

## Product Details


Storage in humid environments can cause the filters to cloud and temperatures should not exceed 50°C for extended periods. Every 0.3 density increment equals one f-stop.

- Available in Large Sizes
- Easily Cut for Custom Sizing
- Kodak Filter No. 96

Kodak Wratten 2 Neutral Density Filters are used in image forming optical systems to reduce light intensity across the visible spectrum without altering the spectral profile. These ND filters feature tolerances of  $\pm 10\%$  of the nominal diffuse density. Although the filters transmit the infrared spectrum, neutrality is controlled only in the visible spectrum. Kodak Wratten 2 Neutral Density Filters are uncoated and have a blocking wavelength range of 400-700nm. All ND filters are 0.1mm in thickness and can be cut for easy custom sizing.

**Note:** Storage in humid environments can cause the filters to cloud and temperatures should not exceed 50°C for extended periods. Every 0.3 density increment equals one f-stop.

## Technical Information



## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools