

Coherent® High Sensitivity Optical Power Sensor 1098318 | 1000:1 Attenuator

See More by [Coherent®](#)



#59-970 Coherent® High Sensitivity Optical Power Sensor 1098318 | 1000:1 Attenuator

Stock **#59-970** 1 In Stock

-

1

+

€560^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€560,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
±5	Calibration Uncertainty (%):
#59-979 and #59-980	Compatible Laser Models:

Optical Properties	
400 - 1800	Wavelength Range (nm):

1100:1 to 950:1		Min. to Max. Attenuation:
Electrical		
Maximum Incident Power Density (mW/cm²):		100
Regulatory Compliance		
Compliant	RoHS 2015:	
Compliant	Reach 224:	
View	Certificate of Conformance:	

Product Details

- Utilize Silicon or Germanium Detectors
- Ideal for nW to Low mW CW Laser Measurements
- Removable Light Shield
- Compatible with [Coherent® Laser Power and Energy Meters](#)

Coherent® High Sensitivity Optical Power Sensors are semiconductor sensors designed for nanowatt to low milliwatt continuous wave laser measurements. These semiconductor sensors are available for detection from the ultraviolet to the infrared, and feature a removable light shield. An attenuator is also available that will boost power up to 5W.

Note: OP-2 sensors are compatible with the LabMax-Pro ([#35-203](#)), LabMax-TOP/TO ([#88-412](#)), FieldMaxI-TOP/TO ([#66-277](#)), and FieldMate ([#59-978](#)) meters.