


[See all 26 Products in Family](#)

TECHSPEC[®] 1050nm, 25mm Diameter, Low GDD Dichroic Shortpass Ultrafast Filter



TECHSPEC[®] Low GDD Dichroic Shortpass Ultrafast Filters

Stock **#14-032** **2 In Stock**

-

1

+

€206⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€206,00 each
Qty 6-25	€165,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Dichroic Filter

Type:

Physical & Mechanical Properties

25.00

Diameter (mm):

1.05 ±0.1

Thickness (mm):

Dimensional Tolerance (mm):	
+0.0/-0.2	
Optical Properties	
Angle of Incidence (°):	
45	
Cut-Off Wavelength (nm):	
1,050.00	
Substrate: ☐	
Fused Silica (Corning 7980)	
Coating:	
Hard Coated	
P-Polarization Transmission (%):	
>80	
Reflection (%):	
>97 Average Polarization	
Reflection Wavelength (nm):	
1102 - 1365	
S-Polarization Transmission (%):	
>80	
Surface Quality:	
60-40	
Transmission (%):	
>85 Average Polarization	
Transmission Wavelength (nm):	
546 - 1008	
Transmitted Wavefront, RMS:	
λ/4	
Slope Factor (%):	
3.00	
Cut-Off Tolerance (%):	
±2	
S-Polarization Reflection (%):	
>95	
P-Polarization Reflection (%):	
>95	
Coating Specification:	
Surface 1: Hard Dielectric Sputtered Surface 2: AR Coated	
Wavelength Range (nm):	
546 - 1365	
GDD Specification (Transmission):	
80 ±30fs ² @ 546 - 625nm 120 ±80fs ² @ 746 - 1008nm	

Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 235:	
Compliant	

Product Details

- Reduced Thickness for Limited GDD
- Broad Transmission and Reflection Ranges
- Ideal for Ultrafast Laser Applications
- Controlled GDD Specification Using [In-House Metrology](#)

TECHSPEC® Low GDD Dichroic Shortpass Ultrafast Filters feature thin substrates and a low group delay dispersion (GDD) coating, making them ideal for use with ultrafast laser sources. Designed for a 45° angle of incidence and covering a range of wavelengths, these spectral filters can be used with Ti:sapphire, Nd:doped, and Yb:doped fiber or glass lasers, as well as with optical parametric oscillators and amplifiers. TECHSPEC Low GDD Dichroic Shortpass Ultrafast Filters are ideal for ultrafast laser applications including multi-photon microscopy, nonlinear fluorescence, and femtosecond stimulated Raman spectroscopy. Please contact us if your application requires an ultrafast optical filter with a custom size or wavelength range.

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). Atypical LIDT for these filters is 1 J/cm² @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Compatible Mounts
