

**TECHSPEC® 1.0mm Diameter, Fused Silica Ball Lens**



Stock #67-380 **20+ In Stock**

⊖ 1 ⊕ €60<sup>.50</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€60,50 each
Qty 11-49	€48,25 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Ball Lens **Type:**

**Physical & Mechanical Properties**

1.00 **Diameter (mm):**

±2.5 **Diameter Tolerance (µm):**

## Optical Properties

Fused Silica (Corning 7980)

Substrate:

Uncoated

Coating:

200 - 2200

Wavelength Range (nm):

1.458

Index of Refraction ( $n_d$ ):

0.625

Sphericity ( $\mu\text{m}$ ):

## Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Compliant

Reach 247:

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details


- Excellent UV Transmission
- Low Coefficient of Thermal Expansion
- Ball and Half-Ball Options Available

TECHSPEC® Fused Silica Ball and Half-Ball Lenses feature high transmission from 200nm to 2.2 $\mu\text{m}$  with a low coefficient of thermal expansion, making it ideal for the most demanding ball lens applications in the ultraviolet, visible, and near-infrared spectra. Ball lenses are commonly used for improving signal coupling between fibers, emitters, and detectors, as well as objective lenses in endoscopy and bar-code scanning applications. Half-ball lenses simplify handling and integration. TECHSPEC Fused Silica Ball and Half-Ball Lenses are uncoated with a fused silica substrate. The lenses are available in diameters ranging from 0.50 to 5.00mm.

## Technical Information



UV FS Transmission Curve



## Compatible Mounts