

10mm Square Microlens Array Mount, 0.9mm Thick



Microlens Array Mounts

Stock **#25-834** 13 In Stock

-

1

+

€78⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-25	€78,80 each
Qty 26+	€70,97 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Fixed

Type of Optics:

Square	
Physical & Mechanical Properties	
9.2 x 9.2	Clear Aperture CA (mm):
25.4	Outer Diameter (mm):
Construction:	
Black Anodized Aluminum	
Min. Thickness of Compatible Optics (mm):	
0.90	
Max. Thickness of Compatible Optics (mm):	
0.90	
Threading & Mounting	
Size of Compatible Optics (mm):	
10.00	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 233:	
Compliant	

PRODUCT DETAILS

- Easily Integrate Microlens Arrays into Optical Applications
- Compatible with Various 25.4mm Outer Diameter [Circular Optical Mounts](#)
- Includes Allen Wrench and M2 Screws

Microlens Array Mounts are designed to facilitate integration of 10mm square Microlens Arrays into optical applications. With an outer diameter of 25.4mm (1"), these mounts are specifically designed to be inserted into our [C, S, and T-Mount Circular Optic Mounts](#), [SM Lens Tubes](#), and our [Compact Mirror and Lens Mounts](#). Microlens Array Mounts are constructed from black anodized aluminum and include an Allen wrench and two M2 Screws which secure the array within the mount. For permanently mounting a Microlens Array into a Microlens Array Mount, we recommend using [Norland Optical Adhesive](#), [NOA 61](#), or [NOA 81](#); curing the adhesive can be achieved using our range of [UV Curing products](#).