


[See all 7 Products in Family](#)

10X Mitutoyo Telecentric Objective

See More by [Mitutoyo](#)



3X (#56-985) & 5X (#56-986)



Stock #56-987 **2 In Stock**

€1.515⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.515,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

375-039 **Model Number:**

Microscope Objective **Type:**

Finite Conjugate **Style:**

Mitutoyo **Manufacturer:**

Note:
Image is formed 280mm from specimen (170mm from the mounting flange)

Physical & Mechanical Properties

59.00 **Length (mm):**

59.00 **Length excluding Threads (mm):**

30 **Maximum Diameter (mm):**

95 **Weight (g):**

Optical Properties

0.64mm **Horizontal Field of View, 1/2" Sensor:**

0.88mm **Horizontal Field of View, 2/3" Sensor:**

17.50 **Focal Length FL (mm):**

NA0.21 **Aperture (f#):**

10X **Magnification:**

0.21 **Numerical Aperture NA:**

1.31 **Resolving Power (μm):**

6.20 **Depth of Field (μm):**

1.8 **Field of View, 18 Diameter Field Eyepiece (mm):**

2.4 **Field of View, 24 Diameter Field Eyepiece (mm):**

51 **Working Distance (mm):**

435 - 655 **Wavelength Range (nm):**

110 **Parfocal Length (mm):**

N/A **Immersion Liquid:**

11.00 **Maximum Image Circle (mm):**

Sensor

2/3" **Maximum Sensor Format:**

Threading & Mounting

M26 x 36 TPI **Mount:**

M26 x 36 TPI **Mounting Threads:**

Environmental & Durability Factors

+5 to +40 **Operating Temperature ($^{\circ}\text{C}$):**

20 - 80% **Operating Humidity:**

Regulatory Compliance

Exempt **RoHS 2015:**

View **Certificate of Conformance:**

Contains SVHC(s) **REACH 241:**

Product Details

- Long Working Distances Allow for Integration into Machine Vision Measurement Systems
- Compact Design and Long Parfocal Length Simplifies Mounting
- [Tube](#) Available for Use with C-Mount Cameras
- Aluminum Alloy Housing

Mtutoyo Telecentric Objectives are ideal for high-resolution, high power machine vision measurement and optical gauging systems. With powers up to 100X, these objectives can be used for semiconductor production and inspection, and in metrology, quality assurance, and R&D laboratories. These objectives are constructed of an aluminum alloy housing. Mtutoyo Telecentric Objectives have a compact design and a long parfocal length that simplifies mounting. They are easily integrated into C-Mount imaging systems with our Mtutoyo C-Mount Camera Tube [#56-992](#).

Edmund Optics is the main source for Mtutoyo Objectives. Place your orders now for these in demand quality products.

Technical Information

Magnification	A	B	C	D	E	Stock No.
1X	49	10	16.5	31.5	31.5	#56-984
3X	33	10	18	25	28	#56-985
5X	49	10	17	25	28	#56-986
10X	59	10	14.5	30	30	#56-987
20X	90	14.5	23	33	39	#87-228
50X	97	14.7	23	33	39	#87-229
100X	104	14.1	23	33	39	#87-230