

[See all 5 Products in Family](#)

## 10X Mitutoyo WLI Plan Apo Objective

See More by [Mitutoyo](#)



10X Mitutoyo WLI Plan Apo Objective

Stock **#74-657** **1 In Stock**

⊖ 1 ⊕ €9.690<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€9.690,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

378-401 **Model Number:**

Compatible Tube Lens Focal Length (mm):  
Focal Length: 100mm

Infinity Corrected **Style:**

Mitutoyo **Manufacturer:**

**Note:**  
Designed to be used with a 100mm Tube Lens, Sold Separately

## Physical & Mechanical Properties

Length (mm):

54.00

Maximum Diameter (mm):

40.00

Weight (g):

220.00

## Optical Properties

Horizontal Field of View, 2/3" Sensor:

0.88mm

Focal Length FL (mm):

10.00

Magnification:

10X

Numerical Aperture NA:

0.38

Resolving Power ( $\mu\text{m}$ ):

0.72

Depth of Field ( $\mu\text{m}$ ):

1.90

Working Distance (mm):

6.00

Field Number (mm):

11.00

Parfocal Length (mm):

60.00

## Sensor

Maximum Sensor Format:

2/3"

## Threading & Mounting

Mounting Threads:

RMS/20.32mm x36 TPI

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Ideal for Interferometry Applications
- Long Working Distances and High Numerical Apertures
- High-Quality Plan Apochromatic Design

Mitutoyo WLI Plan APO Infinity Corrected Objectives are high-resolution plan apochromatic objectives featuring high numerical apertures designed for use in white light interferometry applications. These objectives ensure long parfocal working distances of 60mm while maintaining a more compact and lightweight design. Each objective incorporates an interference fringe adjustment mechanism and internal beam splitter for precise measurements and control of the interference fringe pattern. Mitutoyo WLI Plan APO Infinity Corrected Objectives are available with magnifications ranging from 2.5 – 50x and are designed for use with 100mm focal length tube lenses. These objectives are ideal for white light interferometry applications such as Vertical Scanning Interferometry (VSI), 3D Surface Profiling, Dispersion & Reflection Measurement, and Medical Imaging.