

[See all 1 Products in Family](#)

## 1/2" CCD NIR (1460-1600nm) Analog Camera, CCIR



1460-1600nm Near-Infrared Camera (Front)



Stock #56-848 **3 In Stock**

- 1 + €3.050<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€3.050,00 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

### Product Downloads

NIR

Spectrum:

### General

NIR Camera

Type:

Scintacor

Manufacturer:

## Physical & Mechanical Properties

64.6 x 34 x 37 **Dimensions (mm):**

90.00 **Weight (g):**

Full **Housing:**

## Sensor

1/2" **Sensor Format:**

0.40 **Resolution (Megapixels):**

752 x 582 **Pixels (H x V):**

8.6 x 8.3 **Pixel Size, H x V (µm):**

6.4 x 4.8 **Sensing Area, H x V (mm):**

Interlaced CCD **Type of Sensor:**

1/60 - 1/100,000s **Exposure Time:**

CCIR **Signal Format:**

## Hardware & Interface Connectivity

Analog **Interface:**

BNC **Connector:**

220 V, 50 Hz Included **Power Supply:**

Internal **Synchronization:**

12 VDC, 160 mA **Power Requirement:**

## Threading & Mounting

C-Mount **Mount:**

1/4-20 TPI Tapped **Mounting Threads:**

## Environmental & Durability Factors

-10 to 40 **Operating Temperature (°C):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Low Cost
- Compact Size
- Standard Analog Video Output
- High Speed Electronic Shutter

This near IR camera utilizes a high resolution CCD array that has been specially treated with a phosphor coating. The result is a camera that has an effective response between 1460nm to 1600nm at a cost much lower than seen with other detector technologies. The high-speed electronic shutter allows for easy attenuation of high-level signals often associated with laser applications. Features a maximum CW power saturation of 100mW/cm<sup>2</sup> at 1550nm. The camera is ideal for applications including laser alignment, telecommunication testing, as well as inspection. While standard CCD lenses can be utilized in the near IR, their optical designs and coating are generally not optimized for this region of the spectrum. We recommend video lenses designed specifically for the near IR region.