

12.5/12.7mm 12 Position Motorized Filter Wheel



#88-171 with cover



Stock **#88-398** [CONTACT US](#)

-

1

+

€2.121⁸⁰

ADD TO CART

Volume Pricing	
Qty 1+	€2.121,80 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Adjustable - Rotary

Type:

Circular	Type of Optics:
12	Number of Filters:
Filter Holder Response Time (seconds): Adjacent Locations: 0.8	
Yes	Motorized:
Physical & Mechanical Properties	
±0.25	Repeatability (°):
139.0 x 55.0 x 111.0	Housing Dimension:
Max. Thickness of Compatible Optics (mm): 7.0	
Hardware & Interface Connectivity	
USB Female Micro A	Connector:
+5 VDC, 1.2 A	Power Requirement:
Threading & Mounting	
12.5 - 12.7	Size of Compatible Optics (mm):
M6 x 1.0, 1/4-20, M4 x 0.7, 8-32	Compatible Post:
Environmental & Durability Factors	
0 to 60	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:


PRODUCT DETAILS

- Manual or Automated Multi-Directional Control
- Interchangeable Filter Retaining Wheels
- Lightweight Design with Multiple Mounting Options

Mniature Motorized Filter Wheels are ideal for space constrained applications that require spectral selection, such as fluorescence microscopy, color CCD photography, or photometry. These stepper motor driven, optical encoder regulated filter wheels are designed to repeatedly select absolute positions either manually using a push button or remotely through an RS-232 or USB 2.0 interface. Miniature Motorized Filter Wheels feature two aperture positions, at 12:00 and 9:00, and a digital display which shows the current filter position. The six position filter wheel accepts 25mm filters, while the twelve position filter wheel accepts 12.5mm filters. The base of the unit features six threaded mounting holes to ease system integration, including one 1/4"-20, two #8-32, one M6, and two M4

Note: Accessories are available to increase or decrease compatible filter size.

TECHNICAL INFORMATION



#88-398	
Quantity	Description
1	12.5mm Filter Wheel
1	12 Position Filter Retaining Wheel
1	5VDC Converter
1	USB 2.0A to USB Micro A (6ft cable)
1	RS-232 to RS-232 (6ft cable)

1	Software Flash Drive
2	Threaded Aperture Caps
6	Threaded 1/2" Filter Retaining Rings
1	5/64" Ball Driver
1	Operating Manual

#88-171	
Quantity	Description
1	25mm Filter Wheel
1	6 Position Filter Retaining Wheel
1	5VDC Converter
1	USB 2.0A to USB Micro A (6ft cable)
1	RS-232 to RS-232 (6ft cable)
1	Software Flash Drive
2	Threaded Aperture Caps
6	Threaded 1" Filter Retaining Rings
1	5/64" Ball Driver
1	Operating Manual