


12.7mm Dia., 1mm Thick, Uncoated, ISP Optics Gallium Arsenide (GaAs) Window | GA-W-12-1

See More by [ISP Optics](#)



Gallium Arsenide (GaAs) Windows

Stock **#16-800** CLEARANCE **1 In Stock**

-

1

+

€248⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€248,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Protective Window


Type:

GA-W-12-1	Model Number:
Physical & Mechanical Properties	
Protective as needed	Bevel:
85	Clear Aperture (%):
10.80	Clear Aperture CA (mm):
12.70 +0.00/-0.13	Diameter (mm):
1.00 ±0.13	Thickness (mm):
Fine Ground	Edges:
750.00	Knoop Hardness (kg/mm²):
<3	Parallelism (arcmin):
0.31	Poisson's Ratio:
85	Young's Modulus (GPa):
Optical Properties	
Uncoated	Coating:
3.293 @ 7µm 3.279 @ 10µm 3.267 @ 12µm	Index of Refraction (n _d):
Gallium Arsenide (GaAs)	Substrate:
N/10 @ 10.6µm	Surface Flatness (P-V):
60-40	Surface Quality:
1000 - 16000	Wavelength Range (nm):
Material Properties	
5.39 (0 to +30°C)	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
5.32	Density (g/cm³):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

PRODUCT DETAILS

- Broad Transmission Range from 1 - 16µm
 - Tough, Durable Infrared Material
 - Water Insoluble and Chemically Stable
- ISP Optics Gallium Arsenide (GaAs) Windows transmit infrared light from 1 - 16µm and are opaque in the visible spectrum. Gallium arsenide is a tough, durable material with a Knoop hardness of 750, allowing for its use as a protective window in laser material processing applications where dust, metallic, or abrasive particle debris is expected. ISP Optics Gallium Arsenide (GaAs) Windows are ideal for thermal imaging, forward looking infrared (FLIR), or CO₂ laser applications requiring durable optics. Gallium arsenide is insoluble in water and chemically stable except against strong acids.
- Note:** Gallium arsenide is a hazardous material and should be handled with gloves.

TECHNICAL INFORMATION



SPECIAL HANDLING

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, [cleaning](#), and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools