

[See all 8 Products in Family](#)

TECHSPEC®

128mm Dia x 1900.2mm FL Achromatic Lens



Stock **#70-163** **6 In Stock**

-

1

+

€1.450⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€1.450,00 each
Qty 6-25	€1.305,00 each
Qty 26-49	€1.230,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Achromatic Lens

Type:

Physical & Mechanical Properties

128.02 +0.00/-0.12

Diameter (mm):

124.50

Clear Aperture CA (mm):

5.00	Centering (arcmin):
15.42	Center Thickness CT 1 (mm):
10.92	Center Thickness CT 2 (mm):
-2704.01	Radius R ₄ (mm):
23.87	Edge Thickness ET (mm):
Unmounted, Airspaced 0.10mm	Construction:
Protective as needed	Bevel:

Optical Properties

1,900.24	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
1887.58	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
1,131.72	Radius R ₁ (mm):
-780.87	Radius R ₂ (mm):
-779.37	Radius R ₃ (mm):
N-BK7 / N-SF2	Substrate: □
60-40	Surface Quality:
14.8	f/#:
0.03	Numerical Aperture NA:
MgF ₂ (400-700nm)	Coating:
R _{avg} ≤1.75% @ 400 - 700nm	Coating Specification:
400 - 700	Wavelength Range (nm):

Regulatory Compliance


Compliant	RoHS 2015:
Compliant	Reach 197:
View	Certificate of Conformance:

Product Details

- Offered in Cemented or Air-Spaced Designs
- Mounted Versions Available for Easy Integration
- Feature MgF₂ Anti-Reflection Coating

TECHSPEC® Large Precision Achromatic Lenses offer near-diffraction limited performance across the designated wavelength range. These color-corrected achromatic lenses feature long focal lengths and are available in either cemented or air-spaced designs. The lenses have a MgF₂ anti-reflection coating and are available in diameters up to 140mm. TECHSPEC® Large Precision Achromatic Lenses, in the mounted version, feature a male mounting thread for easy integration into optical systems. Adhesive foil spacers and mounting instructions are included for unmounted, air-spaced achromatic lenses.

Technical Information



Coating Curves

;