

[See all 21 Products in Family](#)

## 1.28mm FL C-Mount, Manual Iris, Wide Angle Lens



1.28mm FL C-Mount, Manual Iris, Wide Angle Lens, #62-050

Stock **#62-050** **2 In Stock**

⊖ 1 ⊕ €783<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€783,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Product Family:  
Low Distortion Wide Angle Lenses

Type:  
Fixed Focal Length Lens

### Physical & Mechanical Properties

Iris Option:  
Variable

Length (mm):

65.10

36.0 **Maximum Diameter (mm):**

36 **Outer Diameter (mm):**

110.00 **Weight (g):**

### Optical Properties

125° **Horizontal Field of View, 1/3" Sensor:**

6.00 **Maximum Image Circle (mm):**

1.28 **Focal Length FL (mm):**

100 - ∞ **Working Distance (mm):**

f/1.8 - Closed **Aperture (f#):**

<3 **Distortion (%):**

<3 **Maximum Distortion (%):**

VS **Lens Wavelength Range:**

### Sensor

1/3" **Maximum Sensor Format:**

4.50 **Pixel Size (µm):**

### Threading & Mounting

N/A **Filter Thread:**

C-Mount **Mount:**

### Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[Contains SVHC\(s\)](#) **Reach 223:**

[View](#) **Certificate of Conformance:**

## Product Details

- Up to 1/2.5", C-Mount and CS-Mount options
- Up to 3 MegaPixel and Down to 1% Distortion
- No Refocusing from 100mm to Infinity
- 1.28mm to 40mm Focal Length

Low Distortion Wide Angle Lenses maintain high resolution for applications with long working distance requirements and can accommodate multi-megapixel camera sensors. The optical design of these low-distortion wide-angle lenses enables users to achieve less than 3% distortion over a 125° field of view, or less than 1% distortion over a 110° field of view. These lenses feature a locking screw for the manual iris enabling the use in high vibration environments. Low Distortion Wide Angle Lenses are ideal for security and surveillance, machine vision, or [factory automation](#) applications. These lenses do not require refocusing from 100mm to Infinity.

**Note:** Image will be flipped (180° rotation). Auto Iris Options require cameras with P-Iris or DC Iris control.