

[See all 6 Products in Family](#)

## 12mm LensConnect BH Series Fixed Focal Length Lens



Computar Motorized LensConnect Fixed Focal Length Lenses

Stock #24-190 **1 In Stock**

[Similar Products](#)

⊖ 1 ⊕ €1.364<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€1.364,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Computar Motorized LensConnect **Product Family:**

DL1224UC-MPY **Model Number:**

Fixed Focal Length Lens **Type:**

Motorized **Special Type of Lens:**

## Physical & Mechanical Properties

Motorized	Iris Option:
57.90	Length (mm):
59.5	Outer Diameter (mm):
163	Weight (g):
59.5 x 57.9	Dimensions (mm):

## Optical Properties

50.5° x 38.1° (D 60.2°)	Horizontal Field of View, 1.1" Sensor:
14.00	Maximum Image Circle (mm):
12.00	Focal Length FL (mm):
100 - ∞	Working Distance (mm):
f/2.4 - f/16	Aperture (f/#):
-0.1	Maximum Distortion (%):
VIS	Lens Wavelength Range:

## Sensor

1/1.1"	Maximum Sensor Format:
12.00	Resolution (Megapixels):
3.45	Pixel Size (µm):

## Hardware & Interface Connectivity

USB2.0 TypeA	Control Interface:
300 ±20	Length of Cable (mm):

## Threading & Mounting

M35.5 x 0.50	Filter Thread:
C-Mount	Mount:

## Regulatory Compliance

<a href="#">View</a>	Certificate of Conformance:
----------------------	-----------------------------

## Product Details

- Focus and Iris Controlled via Simple USB Interface
- 12 MegaPixels, 1/1.1", C-Mount
- Focal Lengths Ranging from 8mm – 50mm
- [Variable Focal Length Option](#) Available

Computar Motorized LensConnect Fixed Focal Length Lenses are designed for remote focus and iris adjustment with a plug-and-play Windows or Linux compatible software. An integrated USB2.0 TypeA connector enables control and provides power to these lenses which are available in focal lengths of 8mm, 12mm, 16mm, 25mm, 35mm, and 50mm. Computar Motorized LensConnect Fixed Focal Length Lenses deliver high resolution for 12MP sensors, and the stepper motors enable precise focus control and high repeatability. These lenses are ideal for machine vision, inspection, and space constrained applications where manual adjustments are not possible.