

[See all 67 Products in Family](#)

# LightPath 354220 | 1310nm Alignment, 0.25 NA Fiber Collimator w/ SMA Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock #47-223 **20+ In Stock**

- 1 + €232.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1-10   | €232,00 each                  |
| Qty 11-25  | €205,00 each                  |
| Qty 26-49  | €193,00 each                  |
| Need More? | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

354220 **Lightpath Lens Code:**  
Fiber Collimator **Type:**

#87-119

Lens Included:

## Physical & Mechanical Properties

5.50 Clear Aperture CA (mm):

Protective as needed Bevel:

304L Stainless Steel Housing Construction:

11.00 Housing Diameter (mm):

17.1 Housing Length (mm):

## Optical Properties

11.00 @ 633nm Effective Focal Length EFL (mm):

0.25 Numerical Aperture NA:

D-ZK3 Substrate: □

BBAR (1050-1600nm) Coating:

R<sub>abs</sub> <1.0% @ 1050 - 1600nm Coating Specification:

40-20 Surface Quality:

2.00 f#:

61.16 Abbe Number (v<sub>d</sub>):

1.586 Index of Refraction (n<sub>d</sub>):

1050 - 1600 Wavelength Range (nm):

Infinite Conjugate Distance:

633.00 Focal Length Specification Wavelength (nm):

1310 Alignment Wavelength (nm):

< 0.040 Transmitted Wavefront Error (λ, RMS):

## Hardware & Interface Connectivity

SMA Connector:

## Threading & Mounting

M11 x 0.5 Mount:

## Material Properties

7.6 Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):

## Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 247:

## Product Details

- Easy to Integrate
- Models for FC/PC, FC/APC, and SMA Connections Available
- Four Wavelength Ranges Covering 350-1600nm

LightPath® Fiber Optic Collimators are designed to collimate light exiting a fiber to a desired beam diameter or spot size or to focus light into a fiber when used in reverse. The lenses are diffraction limited, so they can achieve spot sizes down to a few microns. Lenses also feature an antireflection coating for low back reflection. LightPath® Fiber Optic Collimators are designed so that they can be used in pairs to couple the input and output light of optical devices. Optimum performance for long-term use is ensured by the factory set and tested lens alignment. Typical applications can include use with fiber coupled lasers and pigtailed receptacles, as well as communications and data transfer.

# Technical Information

