

[See all 13 Products in Family](#)

Coherent® Micro VLM™ Laser Diode 0221-155-00 | 1.6mW 670nm 30° Line

See More by [Coherent®](#)



Coherent® Micro VLM™ Laser Diode - Line Option

Stock **#52-268** **4 In Stock**

-

1

+

€219^{,00}

ADD TO CART

Volume Pricing	
Qty 1+	€219,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

Micro VLM		Type:
Fully Shielded, Reverse Polarity Protected		Drive Circuitry:
Diode		Type of Laser:

II		Laser Class - CDRH:	
Standard 9 V Battery: 5		Operating Lifetime (hours):	
Physical & Mechanical Properties			
+0/ - 0.0762		Housing Tolerance (mm):	
15.00		Pointing Accuracy (arcmin):	
0.375		Diameter (inches):	
0.89		Length (inches):	
1.00		Line Width (mm):	
Optical Properties			
670.00		Wavelength (nm):	
±10		Wavelength Tolerance (nm):	
0.2 - 0.3		Wavelength Stability (nm/°C):	
<10		Beam Astigmatism (µm):	
3.00		Beam Diameter (mm):	
<1 transverse to line		Beam Divergence (mrad):	
Red		Color:	
30.00		Fan Angle (°):	
Electrical			
1.6 (Maximum)		Output Power (mW):	
±4		Output Power Tolerance (%):	
ML Spec. Std. 1686B, Class 2		ESD Protection:	
70.00		Current (mA):	
Hardware & Interface Connectivity			
Power Supply Required and Sold Separately. USA: #59-099 Europe: #35-201 Japan: #59-099 Korea: #33-771 China: #59-099		Power Supply:	
3 - 6 VDC		Power Requirement:	
36" Length, Red (+), Black (-), Case (+)		Electrical Leads/ Pin Connections:	
Free Space		Output Type:	
Environmental & Durability Factors			
-10 to +40		Operating Temperature (°C):	
-40 to +80		Storage Temperature (°C):	
Regulatory Compliance			
Exempt		RoHS 2015:	
Contains SVHC(s)		Reach 224:	
View		Certificate of Conformance:	



Product Details

- Robust, High Quality Laser Diodes with Small Form Factor
- 635nm and 670nm High Visibility Wavelengths
- Sophisticated Electronic Design for Consistent Beam Properties

Coherent® Visible Laser Diode Modules feature a compact form factor to help users achieve space saving designs in systems that require a collimated light source. The simple design of these laser diodes allows for quick and efficient incorporation into a wide array of optical systems. A sophisticated electronic design aids in producing consistent laser power and beams. Coherent® Visible Laser Diode Modules with advanced AlignLock™ optical assembly technology provide a remarkable beam-pointing alignment of <4.3mrad, making these laser diodes a great choice for precision applications. These robust, compact laser diodes are typically used in machine vision, medical equipment, and many other industrial applications.

Note: [Power Supply](#), sold separately, is required for operation.

Technical Information



VLM™ High Quality Laser Diode Module - Micro Series