

## 1mW 520nm Mini LDM Laser Diode Module



Stock #72-808 **1 In Stock**

- 1 + €212.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-9	€212,00 each
Qty 10+	€202,00 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads



### General

Index Guided Diode, CW

Type:

Mean Time To Failures MTTF @ 25° (hours):  
≥40,000

Drive Circuitry:  
Fully shielded, reverse polarity protected

Note:  
Includes: Users Manual, Warning Label, and Focus Key

Diode	Type of Laser:
II	Laser Class - CDRH:
<b>Physical &amp; Mechanical Properties</b>	
9.5	Weight (g):
<25	Pointing Accuracy (mrad):
230	Length of Leads (mm):
37.00	Length (mm):
<b>Optical Properties</b>	
520.00	Wavelength (nm):
±15nm	Wavelength Tolerance (nm):
0.25	Wavelength Stability (nm/°C):
<25	Beam Size at Nearest Focus (µm):
4 x2 at Aperture	Beam Diameter (mm):
<0.5	Beam Divergence (mrad):
Green	Color:
35mm - ∞	Focus Range (mm):
<b>Electrical</b>	
<60	Operating Current (mA):
1 (Maximum)	Output Power (mW):
±5	Output Power Tolerance (%):
<b>Hardware &amp; Interface Connectivity</b>	
+10Vdc power supply required	Power Supply:
10 VDC	Power Requirement:
red (+), black (-)	Electrical Leads/ Pin Connections:
Free Space	Output Type:
<b>Environmental &amp; Durability Factors</b>	
-10 to +55	Operating Temperature (°C):
-10 to +85	Storage Temperature (°C):
<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	Reach 240:


## Product Details

- Line Generation Optics Available
- Bare Leads for Instrument Integration
- Focusable from 35mm to Infinity

Self-contained and miniature, laser diode modules offer a variety of features. They are an ideal replacement for a helium-neon laser in many applications, and offer the benefits of superior durability, small size, and a range of wavelengths and powers. Elliptical output beams are produced using a user-adjustable glass focusing lens. Circular output beams are produced using a long focal length plastic lens and are suitable for long distance and alignment applications. Applications include use as pilot beams for alignment, bar code readers, measurement, dimensional scanning, robotic control, target designation, positioning, and analysis. Focusing tool included with all diode modules. Line Generator attachments are available for all diode modules listed. [Power Supply](#), required for operation, sold separately.

**Note:** Laser diode case is electrically isolated from supply voltage.

# Technical Information



;