

[See all 4 Products in Family](#)

TECHSPEC[®]

20mm Uncoated, Fused Silica Penta Prism



Stock

#49-018

CLEARANCE

20+ In Stock

-

1

+

€131^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€131,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Penta Prism

Type:

Physical & Mechanical Properties

±0.10

Dimensional Tolerance (mm):

Protective as needed

Bevel:

Optical Properties

Coating:	
Uncoated	
Substrate: ☐	
Fused Silica (Corning 7980)	
Surface Quality:	
20-10	
Angle Tolerance (arcmin):	
±1	
Image Orientation:	
Right-Handed	
Ray Deviation (°):	
90	
Wavelength Range (nm):	
200 - 2200	
Power (fringes) @ 632.8nm:	
0.20	
Irregularity (fringes) @ 632.8nm:	
0.20	

Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details

• Ray Deviation of 90°


• Right Handed Image

• Optical Tool for Defining a Right Angle


• Additional [Penta Prism](#) Options Available

Penta prisms are five-sided prisms featuring a ray deviation of 90° and a right handed image. The UV-AR coated options also have aluminized reflecting surfaces for increased efficiency. Slight movement of the prism does not affect the true right angle at which light rays are reflected, making a penta prism the ideal optical tool for defining a right angle in an optical system. TECHSPEC® UV Fused Silica Penta Prisms are made from UV fused silica which features low thermal expansion and excellent transmission throughout the UV, VS, and NIR spectral ranges.

Technical Information




UV FS Transmission Curve



>

Stock No.	A	B
#49-016	5.00mm	6.10mm
#49-020		
#49-017	10.00mm	11.95mm
#49-021		
#49-018	20.00mm	21.65mm
#49-022		
#49-019	25.00mm	27.90mm
#49-023		



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
 - High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).