

25.4mm Dia., 2mm Thick, Uncoated, ISP Optics IR Fused Silica Window | QI-W-25-2

See More by [ISP Optics](#)



Stock **#24-585** CLEARANCE **14 In Stock**

-

1

+

€56⁴⁸

€112,95

ADD TO CART

Volume Pricing	
Qty 1+	€112,95 €56,48 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Protective Window

Type:

QI-W-25-2

Model Number:

Physical & Mechanical Properties	
Protective as needed	Bevel:
85	Clear Aperture (%):
21.59	Clear Aperture CA (mm):
25.40 +0.00/-0.13	Diameter (mm):
2.00 ±0.13	Thickness (mm):
Fine Ground	Edges:
522.00	Knoop Hardness (kg/mm²):
<3	Parallelism (arcmin):
0.16	Poisson's Ratio:
73	Young's Modulus (GPa):
Optical Properties	
67.8	Abbe Number (v _d):
Uncoated	Coating:
1.458	Index of Refraction (n _d):
Fused Silica	Substrate:
1λ	Surface Flatness (P-V):
40-20	Surface Quality:
200 - 3500	Wavelength Range (nm):
Material Properties	
Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)	
2.20	Density (g/cm³):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

PRODUCT DETAILS

- Excellent Thermal Stability
- Low Auto-Fluorescence
- IR Grade Fused Silica

ISP Optics Fused Silica Windows feature high transmission across the Ultraviolet (UV), Visible (VIS), and Infrared (IR) spectrum with IR Grade substrates extending up to 3500nm with no absorption bands. Fused Silica is a commonly used material for precision optics due to its consistent and repeatable optical performance. In addition, fused silica features a low coefficient of thermal expansion that provides high thermal stability and resistance to thermal shock. ISP Optics Fused Silica Windows provide extremely low fluorescence, making them ideal for a wide range of UV and IR laser applications.