

[All Products](#) / [Optics](#) / [Polarization](#)
/ [Crystalline Waveplates](#) / [High Energy](#)

[See all 30 Products in Family](#)

25.4mm Dia., 515nm



High Energy Quartz Waveplates

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit

1

€655⁰⁰

ADD TO CART

Volume Pricing

Qty 1-10	€655,00 each
Qty 11+	€610,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

- STEP:step
- Curve:pdf
- PDF Drawing:pdf
- IGES:igs
- eDrawing:eprt
- EO Spec Sheet
- [Download All](#)

General

Type: High Energy Waveplate

Physical & Mechanical Properties

Clear Aperture CA (mm): 18.0

Diameter (mm): 25.40

Dimensional Tolerance (mm): +0/-0.2

Construction: Optically Bonded on UVFS (C7980) Substrate

Parallelism (arcsec): <3

Optical Properties

Coating: R_{avg} <0.2%

Design Wavelength DWL (nm): 515

Substrate: Crystalline Quartz

Retardance: λ/4

Surface Quality: 20-10

Transmitted Wavefront, P-V: <λ/10 @ 632.8nm

Retardance Tolerance: λ/250 @ 20°C

Damage Threshold, By Design: >20 J/cm² @ 1064nm, 10ns, 10Hz

Retardance Order: 1st

Threading & Mounting

Mount Thickness (mm): 6 ±0.2

Regulatory Compliance

RoHS 2015: **Compliant**

Certificate of Conformance: [View](#)

Reach 247: **Compliant**

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Product Details

- Damage Threshold up to $>20 \text{ J/cm}^2$ @ 1064nm
- $\lambda/4$ and $\lambda/2$ Retardance
- Black Anodized Aluminum Mount
- UV to NIR Design Wavelengths Available

High Energy Quartz Waveplates are available in both $\lambda/4$ and $\lambda/2$ retardance for discrete laser wavelengths from the UV to NIR and can withstand energy densities up to $>20 \text{ J/cm}^2$ at 1064nm. A large acceptance angle and wide operating temperature range enables these waveplates to be integrated into harsh environments applications. High Energy Quartz Waveplates are mounted in a black anodized aluminum housing for easy identification and system integration.

Related Products



Compact Direct Mounts



Metric Polarizer Mounts



Rotation Kinematic Mounts

Frequently Purchased Together



#39-169 - 25.4mm Dia., 515nm, $\lambda/2$
High Energy Waveplate
€655,00

Qty



Resources

Media Type

- Application Note
- Technical Tool
- Video
- FAQ
- Glossary

APPLICATION NOTE
Introduction to
Polarization

TECHNICAL TOOL
Laser-Cut
Polymer
Polarizer and
Retarder...

APPLICATION NOTE
Polymer
Polarizers and
Retarders

APPLICATION NOTE

Delivering

APPLICATION NOTE

Understanding

VIDEO

How Do 3D
Movies Work?
Polarization

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

[View More](#)