

**TECHSPEC® 25.4mm Dia., 532nm T, 355nm R 0° Harmonic Separator**



TECHSPEC Nd:YAG Harmonic Separators

Stock #22-663 **20+ In Stock**

⊖ 1 ⊕ €302.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€302,00 each
Qty 6-24	€272,00 each
Qty 25-49	€242,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Harmonic Beamsplitter **Type:**

**Physical & Mechanical Properties**

>85 **Clear Aperture (%):**

**Construction:**

Dichroic

25.40 +0.00/-0.10 **Diameter (mm):**

<3 **Parallelism (arcmin):**

6.35 ±0.20 **Thickness (mm):**

### Optical Properties

0 **Angle of Incidence (°):**

**Coating Specification:**  
Surface 1: R<sub>abs</sub>: >99% @ 355nm, T<sub>abs</sub>: >95% @ 532nm  
Surface 2: R<sub>abs</sub>: <0.5% @ 532nm

355 **Reflection Wavelength (nm):**

**Substrate:**   
[Fused Silica](#) (Corning 7980)

M10 **Surface Flatness (P-V):**

10-5 **Surface Quality:**

532 **Transmission Wavelength (nm):**

**Damage Threshold, By Design:**   
Surface 1: 2.5 J/cm<sup>2</sup> @ 355nm, 20ns, 20Hz  
5 J/cm<sup>2</sup> @ 532nm, 20ns, 20Hz  
Surface 2: 10 J/cm<sup>2</sup> @ 532nm, 20ns, 20Hz

### Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

## Product Details

- Used to Separate Nd:YAG Harmonic Wavelengths
- Beamsplitter Coating Features >95% Transmission
- M10 Fused Silica Substrate

TECHSPEC® Nd:YAG Harmonic Separators are used to separate the common harmonic wavelengths of an Nd:YAG laser. A beamsplitter coating on the first surface reflects at least one wavelength and transmits another. The second surface of the beamsplitter features an anti-reflective coating to minimize the loss due to reflection. TECHSPEC Nd:YAG Harmonic Separators are available in 45° and 0° angle of incidence options. These harmonic separators are available in multiple wavelength configurations for optimal flexibility in system design.

**Note:** The Damage Threshold values we publish for this family of products were all tested independently from one another. When using these products with more than 1 incident beam, the resulting Damage Threshold of the system will be negatively impacted.

## Compatible Mounts