

2.5mm CA NIR, Corning® Varioptic® A-PE Series Variable Focus Liquid Lens Development Kit



Corning® Varioptic® A-PE Series Variable Focus Liquid Lenses



Stock **#73-560** **8 In Stock**

-

1

+

€1.094⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.094,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Development Kit	
Type:	
Contents of Kit:	
Corning® Varioptic® A-PE-25H1-33 Lens USB-MFlexiboard (with 4 and 6 pin connector and USB compatibility)	

Model Number:	
D-APE-25H1-33	
Typical Applications:	
Compact optical systems such as barcode readers, industrial cameras, & medical imaging and biometrics systems	
Physical & Mechanical Properties	
Diameter (mm):	
8.80 (packaged lens)	
Clear Aperture CA (mm):	
2.5	
Thickness (mm):	
2.80 (packaged lens)	
Optical Properties	
Coating:	
NIR	
Focus Range (mm):	
-5 to +13 diopter	
Transmission (%):	
96 @ 850nm	
Transmitted Wavefront Error, RMS:	
30nm	
Environmental & Durability Factors	
Operating Temperature (°C):	
-30 to +60	
Storage Temperature (°C):	
-40 to +85	
Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details

- Combine a Liquid Lens with Dedicated, Calibrated Driver Board
- Temperature Compensation and Response Time Optimization Features
- Include Control Software and Documentation Package
- [A-P Series Liquid Lenses](#) Also Available

Coming® Varioptic® A-PE & V-PE Series Variable Focus Liquid Lens Development Kits feature a variable focus liquid lens with a dedicated, calibrated driver board for enhanced performance, temperature compensation, and response time optimization, as well as all necessary cables and control software for operation. The driver board enables advanced features including temperature compensation algorithms, response time optimization for optical power changes, and sweep mode which acquires clear images while the liquid lens is still in motion. The V-PE Series expands on this technology with an 8-electrode design, enabling independent control of spheres at ±24 diopters of power, cylinders at ±5 diopters of power, and axis for astigmatism correction without any moving parts, ensuring silent, reliable operation. Coming® Varioptic® A-PE & V-PE Series Variable Focus Liquid Lenses are ideal for use in barcode readers, industrial inspection, medical imaging, and biometrics applications and are fully compatible with the [AF Explorer Camera](#) for plug-and-play operation. Also included in the development kit is a documentation package with additional application information.