



[All Products](#) / [Optics](#) / [Optical Lens](#)  
/ [VIS 0° Coated Achromatic Lens](#)

[See all 293 Products in Family](#)

**TECHSPEC® 25mm**



Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit

Options

- 1 +

€138<sup>,00</sup>

ADD TO CART

Volume Pricing

Qty 1-5 €138,00 each

Qty 6-25 €110,00 each

Qty 26-49 €104,00 each

Need More? [Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Product Downloads

- STEP:stp PDF Drawing:pdf
- ISO 10110 Drawing
- IGES:igs Spec Sheets:pdf
- Zemax:zar Zemax:zmx
- eDrawing:eprt Code V:seq
- EO Spec Sheet

**General**

Type: Achromatic Lens

**Physical & Mechanical Properties**

Diameter (mm): 25.00 ±0.025

Clear Aperture CA (mm): 24.00

Centering (arcmin): <1

Center Thickness CT (mm): 5.50 ±0.20

Center Thickness CT 1 (mm): 3.00 ±0.10

Center Thickness CT 2 (mm): 2.50 ±0.10

Edge Thickness ET (mm): 5.13

Bevel: Protective as needed

**Optical Properties**

Effective Focal Length EFL (mm): 500.00

Focal Length Tolerance (%): ±1

Back Focal Length BFL (mm): 497.57

Focal Length Specification Wavelength (nm): 587.6

Radius R<sub>1</sub> (mm): 290.71

Radius R<sub>2</sub> (mm): -232.07

Radius R<sub>3</sub> (mm): -750.52

Substrate: [N-BK7 / N-SF5](#)

Surface Quality: 40-20

f/#: 20.00

<b>Numerical Aperture NA:</b>	0.03	<b>Coating:</b>	VIS 0° (425-675nm)
<b>Coating Specification:</b>	$R_{avg} \leq 0.4\%$ @ 425 - 675nm	<b>Power (P-V) @ 632.8nm:</b>	1.5 $\lambda$
<b>Irregularity (P-V) @ 632.8nm:</b>	$\lambda/4$		

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

**Select Your Country/Region:**

## Regulatory Compliance

RoHS 2015: **Compliant**

Reach 209: **Compliant**

Certificate of Conformance: **View**

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Designed for 0° Angle of Incidence
- Less Than 0.4% Reflectance Per Surface from 425 - 675nm
- **MgF<sub>2</sub>** and **VIS-NIR** Coated Achromats Also Available

TECHSPEC® VIS 0° Coated Achromatic Lenses consist of two optical components cemented together to form an achromatic doublet. The doublet is computer optimized to correct for on-axis spherical and chromatic aberrations. Achromatic lenses are best for applications involving multi-color (white light) imaging due to their specific doublet lens pairing that enables them to correct the color separation inherent in glass. TECHSPEC® VIS 0° Coated Achromatic Lenses provide optimized transmission for 425 – 675nm, reducing average reflection to 0.4%. **MgF<sub>2</sub>** and **VIS-NIR** Coated Achromats are also available on our website.

## Technical Information

## Coating Curves

VIS 0° (425-675nm)



Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

**Select Your Country/Region:**

🔍 SHIFT + SELECT an area on CURVE to zoom

Please note that coating performance outside each product's specified design range is theoretical and may vary.

### Related Products




Optic Component Mounts



C, S, and T-Mount Circular Optic Mounts















Optics Cleaning Brushes



Aspherized Achromatic Lenses

### Compatible Mounts

	Title	Type	Compare	Stock Number	Price	Buy
<a href="#">MORE+</a>	25.0/25.4mm Optic Dia., SM1 Thin Mount, M4	Fixed		#13-787	€21,00 <a href="#">Request Quote</a>	8 In Stock <input type="text" value="1"/>
<a href="#">MORE+</a>	25.0/25.4mm Optic Dia., SM1 Thin Mount, 8-32	Fixed		#13-788	€21,00 <a href="#">Request Quote</a>	20+ In Stock <input type="text" value="1"/>
<a href="#">MORE+</a>	25.0mm Optic Dia., Optic Mount	Fixed		#64-560	€32,75 <a href="#">Request Quote</a>	3 In Stock <input type="text" value="1"/>
<a href="#">MORE+</a>	30mm Cage 25/25.4mm Diameter Thick Lens Mount	Fixed		#85-588	€45,75 <a href="#">Request Quote</a>	20+ In Stock <input type="text" value="1"/>
<a href="#">MORE+</a>	25.0/25.4mm Optic Dia., L-Slot Direct Mount	Fixed		#36-410	€68,00 <a href="#">Request Quote</a>	15 In Stock <input type="text" value="1"/>
<a href="#">MORE+</a>	25.0/25.4mm Optic Dia., Side Flange Direct Mount	Fixed		#36-414	€71,00 <a href="#">Request Quote</a>	20+ In Stock <input type="text" value="1"/>

	Title	Type	Compare	Stock Number	Price	Buy
<a href="#">MORE+</a> 	25mm Thick Inner Pair Optic M				€80,50	5 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	25/25.4mm Diameter, C Thick Optic					5 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	25.0/25.4mm Optic Dia., L-Slot and Rotation Direct Mount	Adjustable - Rotary		#36-411	€102,00 <a href="#">Request Quote</a>	5 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	25.0/25.4mm Optic Dia., X-Y Translating Optic Mount	Adjustable - Linear (XY)		#62-956	€276,00 <a href="#">Request Quote</a>	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	25.0/25.4mm Optic Dia., X-Y-Z Translating Optic Mount	Adjustable - Linear (XYZ)		#62-959	€540,00 <a href="#">Request Quote</a>	6 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	25.0/25.4mm Optic Dia., 5 Axes Optical Mount	Adjustable - Linear (XYZ) & Tip-Tilt		#13-776	€755,00 <a href="#">Request Quote</a>	2 In Stock <input type="text" value="1"/> 

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

**Select Your Country/Region:**

Check out our full selection of mounts [here](#).

# Resources

## Media Type

- Application Note
- Scientific Paper
- Video
- FAQ
- Glossary

**APPLICATION NOTE**

**Anti-Reflection (AR) Coatings**

**APPLICATION NOTE**

**An Introduction to Optical Coatings**

**APPLICATION NOTE**

**Lens Geometry Performance Comparison**

**SCIENTIFIC PAPER**

**Achrotech: achromat cost versus performance...**

**APPLICATION NOTE**

**Why Use an Achromatic Lens?**

**VIDEO**

**Achromatic Lenses Review**

[View More](#)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

**Select Your Country/Region:**