

[See all 33 Products in Family](#)

TECHSPEC® 25mm Dia x 25mm FL, V-Coated, High Precision Aspheric Lens



TECHSPEC® High Precision Aspheric Lenses

Stock **#22-941** **9 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €799⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€799,00 each
Qty 6-10	€719,00 each
Qty 11+	€671,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Aspheric Lens **Type:**

3D Surface Profile not included with coated lenses **Note:**

Physical & Mechanical Properties

25.00 +0.0/-0.025	Diameter (mm):
<2.5	Centering (arcmin):
22.5	Clear Aperture CA (mm):
4.25	Edge Thickness ET (mm):
8.50 ±0.1	Center Thickness CT (mm):
Protective as needed	Bevel:
Plano	Shape of Back Surface:

Optical Properties

25.00 @ 1550nm	Effective Focal Length EFL (mm):
0.50	Numerical Aperture NA:
20.18 @ 1500nm	Back Focal Length BFL (mm):
N-SF6	Substrate: <input type="checkbox"/>
1550	Aspheric Design Wavelength (nm):
λ/40	Asphere Figure Error, RMS @ 632.8nm:
1550nm V-Coat	Coating:
$R_{abs} < 0.25\% @ 1550nm @ 0^\circ AOI$	Coating Specification:
0.016	Asphere Figure Error (μm RMS):
40-20	Surface Quality:
1	f/#:
1550	Design Wavelength DWL (nm):
Infinite	Conjugate Distance:
1550	Focal Length Specification Wavelength (nm):
$5 J/cm^2 @ 1550nm, 10ns$	Damage Threshold, By Design: <input type="checkbox"/>
40.00	Power (diopters):

Environmental & Durability Factors

ADHESION AND ABRASION AS PER ML-PRF13830B APP C, PARA C.3.8.4 AND C.3.8.5	Durability:
---	--------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- High Precision Aspheric Surface
- 3D Surface Profiles Included with Uncoated Lenses
- Uncoated and <0.25% Reflectance V-Coat Available

TECHSPEC® High Precision Aspheric Lenses guarantee better than $\lambda/40$ wave aspheric figure error. Achieved via precision magneto-rheological finishing (MRF), these aspheres offer high numerical apertures with diameters ranging from 15 to 50mm and are ideal for a variety of imaging and low light level applications. Each TECHSPEC High Precision Aspheric Lens is individually measured. 3D surface profiles are included with uncoated lenses. For diffraction-limited aspheres designed at specific Nd:YAG laser wavelengths, see our [TECHSPEC High Precision Laser Grade Aspheric Lenses](#).

;