

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Standard Plano-Convex \(PCX\) Lenses](#)

[See all 25 Products in Family](#)

TECHSPEC® 25mm



Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit

1

€740⁰⁰

ADD TO CART

Volume Pricing

Qty	€740,00
1+	each

Need More?	Request Quote
------------	-------------------------------

Prices shown are exclusive of VAT/local taxes

Product Downloads

[EO Spec Sheet](#)

General

Number of Lenses: 23.00

Type: PCX, DCX, PCV, DCV Lens Kit

Note: See Technical Information tab for focal lengths of included lenses.

Contents of Kit: PCX, DCX, PCV, DCV Lens Kit

Physical & Mechanical Properties

Diameter (mm): 25.00
+0.00/-0.10

Bevel: Protective as needed

Optical Properties

Coating: MgF₂ (400-700nm)

Coating Specification: R_{avg} ≤1.75% @ 400 - 700nm

Wavelength Range (nm): 400 - 700

Regulatory Compliance

Reach 174: [Compliant](#)

Certificate of Conformance: [View](#)

Product Details

- Simple Lens Kits Include PCX, DCX, PCV, and DCV Lenses
- Kits Available for 12mm and 25mm Diameter Lenses
- Uncoated or BBAR Coating Options
- Note: Potential change of packaging

TECHSPEC® Plano-Convex (PCX) and Simple Lens Kits are an ideal complement to any engineering or R&D laboratory. Offered with a variety of coating options, each lens kit contains our highest quality optics with various effective focal lengths. Available uncoated or with broadband anti-reflection (BBAR) coating options. Simple lens kits feature a selection of plano-convex (PCX), double-convex (DCX), plano-concave (PCV), and double-concave (DCV) lenses. These kits are available with 12 or 25mm diameters.

Note: Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact kits@edmundoptics.com.

Technical Information

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Lens Specifications		Coating Options				
Effective Focal Length EFL	f/#	Uncoated (#34-072)	MgF ₂ (#48-101)	VIS 0° (#48-162)	VIS-NIR (#48-162)	NIR I (#65-577)
12.00mm	1.00	#45-083	#45-084	#47-329	#45-480	#48-732
15.00mm	1.25	#45-302	#45-303	#47-330	#45-481	#48-733
18.00mm	1.50	#32-006	#32-007	#47-331	#45-482	#48-734
24.00mm	2.00	#32-011	#31-855	#47-332	#45-483	#48-735
30.00mm	2.50	#45-085	#45-086	#47-333	#45-484	#48-736
36.00mm	3.00	#33-352	#33-353	#33-354	#33-355	#33-356
42.00mm	3.50	#45-123	#45-124	#47-335	#45-485	#48-738
48.00mm	4.00	#32-852	#32-853	#47-336	#45-486	#48-739
54.00mm	4.50	#45-304	#45-305	#47-337	#45-487	#48-740
60.00mm	5.00	#32-854	#32-855	#47-338	#45-488	#48-741
72.00mm	6.00	#45-125	#45-126	#47-339	#45-705	#48-742
84.00mm	7.00	#32-856	#32-857	#47-340	#45-489	#48-743
100.00mm	8.33	#45-274	#45-275	#47-341	#45-490	#48-744

Lens Specifications		Coating Options				
Effective Focal Length EFL	f/#	Uncoated (#65-578)	MgF ₂ (#48-610)	VIS 0° (#48-611)	VIS-NIR (#48-612)	NIR I (#65-579)
25.00mm	1.00	#45-097	#45-098	#47-342	#45-504	#48-766
30.00mm	1.20	#45-364	#45-363	#47-343	#45-505	#48-767
35.00mm	1.40	#45-145	#45-146	#47-344	#45-506	#48-768
40.00mm	1.60	#45-278	#45-279	#47-345	#45-507	#48-769
50.00mm	2.00	#32-477	#32-478	#47-346	#45-508	#48-770
60.00mm	2.40	#45-127	#45-128	#47-347	#45-509	#48-771
75.00mm	3.00	#32-479	#32-480	#47-348	#45-510	#48-772
100.00mm	4.00	#32-481	#32-482	#47-350	#45-512	#48-774
125.00mm	5.00	#32-861	#32-862	#47-351	#45-513	#48-775
150.00mm	6.00	#32-863	#32-864	#47-352	#45-514	#48-776
175.00mm	7.00	#32-865	#32-866	#47-353	#45-515	#48-777
200.00mm	8.00	#33-358	#33-359	#33-360	#33-361	#33-362
400.00mm	16.00	#33-364	#33-365	#33-366	#33-367	#33-368
500.00mm	20.00	#45-280	#45-281	#47-356	#47-387	#48-780

Lens Specifications		Coating Options				
Effective Focal Length EFL	f/#	405nm V-Coat (#66-117)	532nm V-Coat (#66-118)	633nm V-Coat (#66-119)	785nm V-Coat (#66-120)	1064nm V-Coat (#66-121)
25.00mm	1.00	#65-464	#65-484	#65-504	#65-524	#65-544
50.00mm	2.00	#65-465	#65-485	#65-505	#65-525	#65-545
75.00mm	3.00	#65-466	#65-486	#65-506	#65-526	#65-546
100.00mm	4.00	#65-467	#65-487	#65-507	#65-527	#65-547
125.00mm	5.00	#65-468	#65-488	#65-508	#65-528	#65-548

Lens Specifications		Coating Options				
---------------------	--	-----------------	--	--	--	--

Effective Focal Length EFL	f/#	Lens Type	Uncoated (#65-580)	MgF ₂ (#55-249)	VIS 0° (#48-163)	VIS-NIR (#48-539)	NIR I (#66-109)
12.00mm	1.00	PCX	#45-083	#45-084	#47-329	#45-480	#48-732
24.00mm	2.00	PCX	#45-083	#45-084	#47-329	#45-483	#48-735
36.00mm	3.00	PCX	#45-083	#45-084	#47-329	#45-483	#33-355
48.00mm	4.00	PCX	#45-083	#45-084	#47-329	#45-486	#48-739
60.00mm	5.00	PCX	#45-083	#45-084	#47-329	#45-488	#48-741
12.00mm	1.00	DCX	#33-388	#33-389	#33-390	#45-872	#49-474
24.00mm	2.00	DCX	#33-388	#33-389	#33-390	#33-391	#33-392
36.00mm	3.00	DCX	#32-869	#32-870	#47-362	#45-876	#49-478
48.00mm	4.00	DCX	#45-159	#45-160	#47-363	#45-877	#49-479
72.00mm	6.00	DCX	#32-871	#32-872	#47-364	#45-878	#49-480
-12.00mm	-1.00	PCV	#45-014	#45-015	#47-905	#45-916	#49-525
-24.00mm	-2.00	PCV	#45-016	#45-017	#47-906	#45-917	#49-528
-48.00mm	-4.00	PCV	#45-018	#45-019	#47-907	#45-918	#49-530
-12.00mm	-1.00	DCV	#32-988	#32-989	#47-915	#45-928	#49-546

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Lens Specifications		Coating Options					
Effective Focal Length EFL	f/#	Lens Type	Uncoated (#66-110)	MgF ₂ (#52-305)	VIS 0° (#48-613)	VIS-NIR (#48-614)	NIR I (#66-111)
25.00mm	1.00	PCX	#45-097	#45-098	#47-342	#45-504	#48-766
50.00mm	2.00	PCX	#32-477	#32-478	#47-346	#45-508	#48-770
75.00mm	3.00	PCX	#32-479	#32-480	#47-348	#45-510	#48-772
100.00mm	4.00	PCX	#32-481	#32-482	#47-350	#45-512	#48-774
125.00mm	5.00	PCX	#32-861	#32-862	#47-351	#45-513	#48-775
150.00mm	6.00	PCX	#32-863	#32-864	#47-352	#45-514	#48-776
175.00mm	7.00	PCX	#32-865	#32-866	#47-353	#45-515	#48-777
200.00mm	8.00	PCX	#33-358	#33-359	#33-360	#33-361	#33-362
400.00mm	16.00	PCX	#33-364	#33-365	#33-366	#33-367	#33-368
25.00mm	1.00	DCX	#32-489	#32-490	#47-365	#45-887	#49-489
50.00mm	2.00	DCX	#32-624	#32-625	#47-368	#45-890	#49-492
75.00mm	3.00	DCX	#32-626	#32-627	#47-369	#45-891	#49-493
100.00mm	4.00	DCX	#32-717	#32-718	#47-370	#45-892	#49-494
125.00mm	5.00	DCX	#32-873	#32-874	#47-371	#45-893	#49-495
150.00mm	6.00	DCX	#32-875	#32-876	#47-372	#45-894	#49-496
175.00mm	7.00	DCX	#32-877	#32-878	#47-373	#45-895	#49-497
200.00mm	8.00	DCX	#33-394	#33-395	#33-396	#33-397	#33-398
-25.00mm	-1.00	PCV	#45-030	#45-031	#47-911	#45-922	#49-534
-50.00mm	-2.00	PCV	#45-028	#45-029	#47-912	#45-923	#49-536
-100.00mm	-4.00	PCV	#45-026	#45-027	#47-913	#45-924	#49-537
-25.00mm	-1.00	DCV	#32-992	#32-993	#47-917	#45-930	#49-550
-50.00mm	-2.00	DCV	#32-996	#32-997	#47-918	#45-931	#49-551
-100.00mm	-4.00	DCV	#32-994	#32-995	#47-919	#45-932	#49-552

Lens Specifications		Coating Options				
Effective Focal Length EFL	f/#	Uncoated (#66-112)	UV-AR (#66-113)	UV-VIS (#66-114)	VIS 0° (#66-115)	VIS-NIR (#66-116)
38.00mm	1.52	#48-273	#48-283	#48-821	#48-961	#63-806
50.00mm	2.00	#48-274	#48-284	#48-822	#48-962	#63-807
60.00mm	2.40	#48-670	#48-677	#48-823	#48-963	#63-808
75.00mm	3.00	#48-275	#48-285	#48-824	#48-964	#63-809
100.00mm	4.00	#48-276	#48-286	#48-825	#48-965	#63-810


125.00mm	5.00	#48-277	#48-287	#48-826	#48-966	#63-811
150.00mm	6.00	#48-278	#48-288	#48-827	#48-967	#63-812
175.00mm	7.00	#48-279	#48-289	#48-828	#48-968	#63-813
200.00mm	8.00	#48-280	#48-290	#48-829	#48-969	#63-814
250.00mm	10.00	#48-281	#48-291	#48-830	#48-970	#63-815
400.00mm	16.00	#48-282	#48-292	#48-831	#48-971	#63-816

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:


Coating Curves

MgF₂ (400-700nm)



Please note that coating performance outside each product's specified design range is theoretical and may vary.

Frequently Purchased Together



#34-429 - 50mm Dia., 3mm Thick, Uncoated $\lambda/4$ N-BK7 Window
€111,00

Qty



#46-099 - 50.8 x 50.8 x 3mm High Efficiency Window
€28,50

Qty



#48-606 - 12.7mm Silver and VIS 0° Coated, Corner Cube Prism
€289,00

Qty



#53-984 - 4" x 4" Cloth Cleaning Wipes
€36,25

Qty

Resources

Media Type

APPLICATION NOTE

Anti-Reflection (AR) Coatings

APPLICATION NOTE

An Introduction to Optical Coatings

APPLICATION NOTE

Understanding Optical Specifications

- Application Note
- Technical Tool
- Trending in Optics
- FAQ
- Glossary
- Video

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Lens Geometry
Performance
Comparison

SAG Calculator

↑ TRENDING IN OPTICS

Future of
Spherical
Lenses

[View More](#)