

[See all 8 Products in Family](#)

## 25mm FL, Corning® Varioptic® C-C Series C-Mount Liquid Lens Evaluation Kit



Stock #91-610 **NEW** [CONTACT US](#)

1 €1.995<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€1.995,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## General

Development Kit **Type:**

**Contents of Kit:**  
 Coming® Varioptic® C-C-39N0-A1-250 Lens  
 USB-MUniversal  
 USB Cable  
 Focuslab Software  
 Control Software and Documentation Package

## Optical Properties

25.00 **Focal Length FL (mm):**

200 - ∞ **Working Distance (mm):**

f/5 - f/22 **Aperture (f/#):**

VIS **Lens Wavelength Range:**

## Sensor

1.1" **Sensor Format:**

2.74 **Pixel Size (µm):**

## Threading & Mounting

C-Mount **Mount:**

## Environmental & Durability Factors

50 **Operating Temperature (°C):**

45 **Storage Temperature (°C):**

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

## Product Details

- Electronically Controllable Focus
- Ideal For Machine Vision Applications
- Compatible With Up to 1.1", 20mpx Sensors
- C-Mount for Seamless Integration into Imaging Systems

Coming® Varioptic® C-C Series C-Mount Liquid Lens Evaluation Kits feature an electronically controllable liquid lens and integrated driver electronics in a compact, C-Mount design. With rapid switching times, no moving parts, and AR-Coatings for excellent transmission in the VIS and NIR, these lenses are an ideal solution for autofocus applications demanding clarity, durability, and speed. Designed for seamless integration into C-Mount machine vision and imaging systems, the lenses are compatible with sensors up to 1.1". Coming® Varioptic® C-C Series C-Mount Variable Focus Liquid Lenses' integrated electronics allow the lenses to be powered by a simple DC supply and controlled through RS-232, I<sup>2</sup>C, or SPI interfaces. Evaluation kits include Lenses, USB-MUniversal, USB Cable, and Focuslab Software Control Software and Documentation Package.