


[See all 98 Products in Family](#)

## 25µm Aperture Diameter, Molybdenum Aperture



Molybdenum Aperture

Stock #59-255 **5 In Stock**

⊖ 1 ⊕ €131<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-5	€131,00 each
Qty 6-10	€115,90 each
Qty 11+	€107,10 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### Physical & Mechanical Properties

9.5 **Outer Diameter (mm):**

Molybdenum **Construction:**

25.00 **Fixed Aperture Diameter (µm):**

0.05 Nominal	<b>Thickness (mm):</b>
±8	<b>Aperture Tolerance (%):</b>
±125	<b>Aperture Centration (µm):</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>REACH 241:</b>

## Product Details

- Ceramic, Copper, Gold-Plated Copper, Molybdenum, or Tungsten Substrates
- Withstand High Power Densities up to 130MW/cm<sup>2</sup> (For Mo and W Substrates)
- Ideal for Spatial Filtering and Laser Aperturing

High Power Apertures are available in an assortment of available substrates, making them a versatile option for a variety of laser applications. These products are ideal for spatial filtering and as a general aperture. The apertures have an outer diameter of 3/8" (9.5mm). High Power Apertures have one shiny side for high reflectivity while the other is blackened for absorption. The ceramic apertures are white on both sides. The aperture's thickness and the materials' high reflectivity enable them to withstand and quickly dissipate increased irradiation from high-energy lasers. Densities as high as 100MW/cm<sup>2</sup> (130MW/cm<sup>2</sup> for molybdenum and Tungsten substrates) have been used without damage to the apertures.

;